





REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
E		REVISED PER ECO-19-007626	12SEP2019	AP	DG



NOTES:

Housing:PBT+30%GF(UL94V-0) BLACK
Contact:Brass
" GOLD PLATING ON CONTACT AREA
100u" MATTE TIN PLATING ON SOLDER TAIL
50u" NICKEL UNDERPLATED OVERALL
Holddown:Brass,100u" TIN OVER 50u" NICKEL
Shell:Cold Roller Steel,Ni Plated
Revitlock:Brass,Nickel Plating
LOT NUMBER "XXXX"
└─Stands For Calendar Year
└─Stands For Week Number

THREADED	30μAu	2311773-1
-	Contact Area	P/N
	Plating	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN AJITH PAI 10MAR2017	TE Connectivity	
		CHK DANIEL GORENC 10MAR2017		
DIMENSIONS: mm		APVD DANIEL GORENC 10MAR2017	NAME AMPLIMITE PLUG, HD22, RIGHT ANGLE, 62P,Threaded	
		PRODUCT SPEC 108-130023	-	
		APPLICATION SPEC -	-	
MATERIAL -		WEIGHT	SIZE A1	CAGE CODE 00779
			DRAWING NO. 2311773	RESTRICTED TO -
			SCALE 1:1	SHEET 1 of 1
			REV E	