



YAV16M10

by Burndy
Catalog ID: YAV16M10

Copper Tubing Terminal, 1 Hole W/insp window, 16 mm Class 2,5, 7 Index, 10 mm Stud

Product Details

General

Connector Type	Terminal
Die Index	7
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	YES
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810459225
UPC 12 Digit	7818104592255

Dimensions

Dimension - B Length inch	0.50 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	10.4 mm
Dimension - Inside Diameter inch	0.22 in
Dimension - L Length Overall mm	40.9 mm
Dimension - Length Overall inch	0.06 in
Dimension - N inch	0.39 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Pad Width inch	0.58 in
Dimension - Strip Length inch	0.51 in
Dimension - Stud Size inch	#10
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)