TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved







✔ Active

TE CONNECTIVITY (TE)

TERMINAL

Open Barrel Rings & Spades | Open Barrel Rings & Spades

880219-4
TE Internal Number: 880219-4

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Terminal Type Ring Tongue

Stud Diameter 6.5 mm [.256 in]

Tongue Thickness 1.59 mm [.063 in]

Wire Size (AWG) 17 – 13

Wire Size (mm^2) 1 – 2.5

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

Ring Tongue Antirotational
PDF **(TIFF AVAILABLE)**
English

CAD Files

3D PDF
PDF
English

Customer View Model

Downloaded from Arrow.com.

2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Product Specifications

Product Specification

Crimping Extruded Ring Terminals
PDF
English

Crimping AMPLIVAR Ring Terminals
PDF
English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Sealable No
Barrel Type Open Barrel
Wire/Cable Type Regular Wire
Insulated No
Insulated Wire Support Yes
Support Style Insulation Support
Barrel Style Standard
Terminal Features Sheared
Shape Code RING-035
Wire/Cable Composition Solid or Stranded

Configuration Features

Number of Holes 1
Terminal Angle Straight

Body Features

Plating Material Tin
Weight per Piece (g) 3.288
Inspection Slot No

Contact Features

Terminal Type Ring Tongue
Terminal Orientation Straight

Downloaded from Arrow.com.

Dimensions

Stud Diameter 6.5 mm [.256 in]
Tongue Thickness 1.59 mm [.063 in]
Wire Size (AWG) 17 – 13
Wire Size (mm²) 1 – 2.5
Wire Insulation Diameter 2.4 – 3.7 mm [.094 – .146 in]

Operation/Application

Heavy Duty No

Industry Standards

Government Qualified No

Packaging Features

Packaging Method Loose Piece
Packaging Quantity 4000

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance
PDF

Downloaded from Arrow.com.