
Data sheet

H1,5/18D SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- supplied loose in poly-bag
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 15 mm, 12 mm, black
Order No.	9019140000
Type	H1,5/18D SW
GTIN (EAN)	4008190046026
Qty.	500 items
Packaging	loose

Downloaded from Arrow.com.

Data sheet

H1,5/18D SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.13 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule with plastic collar, black	Version	Standard

Wire-end ferrules

Contact surface diameter (D1)	1.7 mm	Contact surface length (L2)	12 mm
Collar diameter (D2)	3.5 mm	Plastic collar thickness (S2)	0.25 mm
L1 in mm	18.00 mm	Wire connection cross section AWG, max.	AWG 16
Metal sleeve thickness (S1)	0.15 mm	Military designation	T 20A 014 A
Stripping length	15 mm	Conductor cross-section	1.5 mm²
Colour code	DIN		

Classifications

ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		


Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing



Downloaded from Arrow.com.