Part Number : 197124001
Product Description : PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 2.79 x 0.51mm, Carton
Series Number : 19712
Status : Active
Product Category : Quick Disconnects



Documents and Resources

Drawings

197124001_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not saleable
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-DC (05 Nov 2025) SCIP:9b57ad9e-307b-418e-a95f-35bbea3c472a
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19712
Description	PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 2.79 x 0.51mm, Carton
Product Name	PCB Tab
Type	PCB Tab
UPC	800755104936

Agency

UL	E79133

Electrical

Voltage - Maximum	N/A

Physical

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulated	No
Insulation	None

Downloaded from Arrow.com.

Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.135/g
Orientation	PCB Straight Tab
Packaging Type	Carton
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	2.79mm
Termination Interface Style	Through Hole
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

Downloaded from Arrow.com.