



Part Number : [451320603](#)
Product Description : Micro-Fit TPA-to-Micro-Fit TPA
Off-the-Shelf (OTS) Cable Assembly, Dual Row,
300.00mm Length, 6 Circuits, Black
Series Number : 45132
Status : Active
Product Category : Power and Signal Cable
Assemblies



Documents & Resources

Drawings
[451320603 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	45132
Description	Micro-Fit TPA-to-Micro-Fit TPA Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, 6 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit TPA Both Ends
Product Name	Micro-Fit TPA
Type	Discrete Wire Assembly
UPC	889056745253

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	300V

Physical

Cable Length	300.00mm
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon

Net Weight	16.468/g
Number of Rows	2
Overmolded	No
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1007
Wire Size (AWG)	20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Headers	<u>43045</u>
Micro-Fit TPA Dual Row Plug Housings	<u>203632</u>
Micro-Fit 3.0 Dual Row Plug Housings	<u>43020</u>

This document was generated on Sep 18, 2025