
Part Number : 190990035
Product Description : InsulKrimp Snap Spade for 16-14 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier, Length 23.34mm, Blue
Series Number : 19099
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : BB-2717-10XT



Documents and Resources

Drawings

190990035_sd.pdf

Specifications

PS-19902-009-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19099
Description	InsulKrimp Snap Spade for 16-14 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier, Length 23.34mm, Blue
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade Snap
Type	Spade Connector
UPC	800753089242

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.859/g
Packaging Type	Adhesive Tape on Reel

Downloaded from Arrow.com.

Stud Size	10 (M5)
Wire Insulation Diameter	4.40mm max.
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638850400

Downloaded from Arrow.com.