





PRODUCT NUMBER	PITCH
HAxx70x000J0G	3.81 mm



RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:

- Item ① Terminal body Thermoplastic (UL94V-0)
- Item ② Terminal cover Thermoplastic (UL94V-0)
- Item ③ Terminal lever Thermoplastic (UL94V-0) Orange(RAL2011/P)
- Item ④ Solder pin Brass, Tin plated
- Item ⑤ Spring clamp Stainless steel

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 6A
- Solid wire(AWG): 16-26
- Stranded wire(AWG): 16-26
- Wire strip length: 9-10 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: cULus

N=Number of poles
Dim L=Nx3.81+2.5
Dim B=(N-1)x3.81

POLES	Tolerance
2-5p	±0.10
6-10p	±0.15
11-15p	±0.20
16-20p	±0.25
21-24p	±0.30

PART NO.: HA xx 70 x 0 00J0 G

		Color	RoHS compliant
End stackable 0		Black (RAL9005)	(lead<4%)
No. of poles 2		Red (RAL3001/D)	In copper Alloy
02 2 poles 3		Orange(RAL2011/P)	
03 3 poles 4		Yellow(RAL1018/A)	
... .. 5		Green(RAL6018/T)	
24 24 poles 6		Blue (RAL5015/A)	
		8 Grey(RAL7004/P)	
		9 White(RAL1102)	
		C Multiple colors	

mat'l. code				surface	tolerance	projection	product family		
ltr ecn no dr date				ASME Y14.5	ASME Y14.5	MM	TERMINAL BLOCK		
				tolerances unless otherwise specified			title		
				angles	X.±0.5		TERMINAL BLOCK		
				fil	X.X±0.3		SPRING CLAMP, 90D WIRE INLET		
				X*±1°	X.XX±0.1	scale	dwg no sheet 1 of 1 size		
				dr	EVIN ZHONG 052314		HAxx70x000J0G A4		
				enr	EVIN ZHONG 052314				
				chr	HANKE FENG 052314				
				appd	SHI JUN 052314		type CUSTOMER Drawing		
sheet index	revision sheet	A	1						