

Part Number : [1731110383](#)

Product Description : FCT Plastic Backshell for D-Sub Connector, Gray, Shell Size 2, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws

Series Number : 173111

Status : Active

Product Category : D-Sub Backshells

Engineering Number : FPHGR-2


Documents & Resources

Drawings

[Drawing 1731110383_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Plastic Backshell for D-Sub Connector, Gray, Shell Size 2, Straight or 90° Angle Cable Outlet, Flat Body, with Grip Cover and #4-40 Locking Screws
Magnetic	Yes
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Type	Plastic
UPC	191128757089

Electrical

Shield Type	None
Shielded	No

Physical

Cable Diameter	8.00mm
Color - Resin	Gray
Material - Backshell	PBT
Material - Screw	Steel
Mounting Style	Locking Screw
Net Weight	19.100/g
Orientation	Straight or 90° Angle
Packaging Type	Carton
Plating - Backshell	None
Temperature Range - Operating	-55° to +140°C
Thread Size	4-40 UNC
Tightening Test Torque	40 Ncm
Waterproof / Dustproof	No

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 2

This document was generated on Sep 01, 2024