

Han-INOX® 24B-HSE-M32 f.DL



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 024 0527
Specification	Han-INOX® 24B-HSE-M32 f.DL
HARTING eCatalogue	https://b2b.harting.com/19440240527

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-INOX®
Type of hood/housing	Hood

Version

Size	24 B
Version	Side entry
Cable entry	1x M32
Locking type	Double locking lever
Field of application	Hoods/housings for harsh environments

Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant



Pushing Performance
Since 1945

Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	0.01 g
Country of origin	Romania
European customs tariff number	85389099
GTIN	5713140829459
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors