Part Number : 192760004

Product Description : Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Continuous Strip

Series Number : 19276

Status : Active

Product Category : Quick Disconnects

Engineering Number : BB-2206C-LIF

Documents & Resources

Drawings

Drawing 192760004_sd.pdf

3D Models and Design Files

3D Model 192760004_stp.zip

Specifications

Product Specification PS-19902-011-001.pdf

Product Specification PS-19902-012-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19276
Description	Quixon Quick Disconnect, InsulKrimp Style, Female, Fully Insulated Blue, 14-16 AWG, Continuous Strip
Comments	Low Insertion Force
Product Family	Quixon Terminals
Product Name	InsulKrimp,Quixon
Type	Quick Disconnect
UPC	884982565104

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Female
Glow-Wire Capable	No
Insulated	Fully
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin

Downloaded from Arrow.com.

Material - Plating Termination	Tin
Net Weight	0.959/g
Orientation	Straight
Packaging Type	Reel
Tab Thickness	0.41mm
Tab Width	7.87mm
Temperature Range - Operating	-55° to +105°C
Wire Insulation Diameter	4.06mm
Wire Size (AWG)	14, 16

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638834200

This document was generated on Jul 29, 2024

Downloaded from Arrow.com.