

Product Information



Part Number:	MU075C070AQ	Document
Series:	General Driver-Outdoor Use	CB Certificate.pdf
Size:	177.0 mm × 67.5 mm × 37.0 mm	CCC Certificate.pdf
Driver Type:	Constant Current	CE Certificate.pdf
Output Power:	75.0 W	Constant Voltage CE Certificate.pdf
Material:	Metal	Constant Voltage UL Certificate.pdf
Dimming Mode:	Non-Dimming	MU075CxxxAQ.pdf
Number of Outputs:	1	TUV MARK Certificate.pdf
Input Voltage:	90-305VAC	UL Certificate.pdf
Mechanical Construct:		
Surge Level:	L-N:4KV L/N-FG:6KV	
Vout:	54-108 V	
Iout:	700.0 mA	
IP Rating:	IP67	
Compliance:	CCC,CE,UL/CUL,CB	
NTC:		
Notes:		
Auxiliary Output:		
Installation Type:		