

Connection Systems Catalog

Search by part# or keyword



FIND BY FEATURE

BROWSE BY CATEGORY

COMPARISON LIST (0)

CUSTOMER SERVICE

REQUEST SAMPLES

SEARCH RESULTS (1)

SEARCH OPTIONS

1 Result(s): [All] - 13587354

☐ Compare



☐ 13587354 32 Way Natural MTS 0.64 Unsealed Female Connector, Max Current 8 amps

☐ Compare

32 Way Natural MTS 0.64 Unsealed Female Connector, Max Current 8 amps



Part # 13587354

[Question about this product?](#)

ATTRIBUTES

DOCUMENTS (2)

RELATED PRODUCTS (5)

Units:

Metric

English

Attributes

Part #	13587354
Description	32 Way Natural MTS 0.64 Unsealed Female Connector, Max Current 8 amps
Product Type	Connector
Status	✓ Active
Product Segment	Standard Automotive
Family	MTS
Series	0.64
Cavities	32
Terminal(s) blade size [mm]	0.64
Sealable	Unsealed
Gender	Female
Material	PBT
Connector Color	Natural
Temperature range (c°)	-40 to 85
RoHs compliant :	✓ Yes
ELV compliant :	✓ Yes
Application	Instrument Cluster,Module - GPS / GSM