

# RDP INPUT CORD & CONNECTOR SET - 8 FOOT

PDW8IEC309-RDP2

Discontinued on: Jul 2, 2025

① Discontinued

## Overview

Lead time Usually Ships within 2 Weeks

### Main

Main Input Voltage	208 V
Main Output Voltage	208 V
Input Connection Type	IEC 60309
Number of cables	1
Provided Equipment	Installation guide

## **Physical**

Height	5.00 in (12.7 cm)
Width	24.02 in (61 cm)
Depth	95.98 in (243.8 cm)
Net Weight	29.28 lb(US) (13.28 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

## Input

permissible voltage	200240 V
Max line current	80 A

## **Output**

Maximum Total Current Draw per Phase	80 A
Number of power socket outlets	1 IEC 60309 32 A
Cord Length	8 ft (2.4 m)

# Ordering and shipping details

GTIN 731304252740

## **Packing Units**

Unit Type of Package 1 PCE

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Nbr. of units in pkg.

4

# **Contractual warranty**

Warranty

2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

#### 

EU RoHS Directive

Under investigation