

Pneumatic module for 3 contacts




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 003 3501
Specification	Pneumatic module for 3 contacts
HARTING eCatalogue	https://harting.com/09140033501

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® Pneumatic module
Size of the module	Single module

Version

Gender	Male
	Female
Number of contacts	3
Details	Please order contacts separately.

Technical characteristics

Limiting temperature	-40 ... +85 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3)
	R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1
UL / CSA	UL 1977 ECBT2.E235076
	CSA-C22.2 No. 182.3 ECBT8.E235076

Commercial data

Packaging size	2
Net weight	0.25 g
Country of origin	Germany
European customs tariff number	39269097
GTIN	5713140162082
eCl@ss	27440220 Module for industrial connectors (pneumatic)
ETIM	EC000438
UNSPSC 24.0	39121552