

C-HVSLS600063XXXX

REV	ECN	DESCRIPTION	DATE	MODIFIED
1		PRE-RELEASE	08/11/16	RY

CUSTOMER DRAWING





HOW TO ORDER

HVSLS 600 06 3X X XX

- A: CODING A
- B: CODING B
- C: CODING C
- 0: WITHOUT HVIL
- 1: WITH HVIL
- 25: CROSS-SECTION 25mm^2 WIRE OD=11.9 ± 0.3mm
- 16: CROSS-SECTION 16mm^2 WIRE OD=11.2 ± 0.25mm

NOTES:

1. ELECTRONICAL CHARACTERISTICS:
   HIGH VOLTAGE RATED 1000 V DC MAX.
   CURRENT RATED 120 A MAX.
   WITHSTANDING VOLTAGE 3000 V AC
   PRODUCTS ARE COMPLIANCE WITH EN 60664-1 POLLUTION II
2. ENVIROMENT CHARACTERISTICS:
   IP67 IP6K9K RATED (WHEN MATING)
   IP2XB RATED FOR FINGER TOUCH-PROOF

DIMENSIONS: ANSI Y14.5M; UNITS: MM; Pro/E FILE	TOLERANCES: .X ±0.5; .XX ±0.20; ANGLES ±0.5°	PROJECTION	Amphenol Pcd Shenzhen	TITLE: HVSLS600 06 3X X XX STRAIGHT PLUG ASSEMBLY
			ENGR: RY 08/11/16	
ORIGINAL — NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN		CHKD:	SIZE: A3 / DWG NO.: C-HVSLS600063XXXX / REV: 1
			APPD:	CODE: 58982 / SCALE: 1:1 / SHEET 1 OF 1

C-HVSLS600063XXXX

C-HVSLS600063XXXX

Downloaded from Arrow.com.