Part Number : 731160076
Product Description : MCRF Right-Angle Plug to Pigtail on 0.81mm Cable, 230.13mm Length, H18, 50 Ohms
Series Number : 73116
Status : Obsolete
Product Category : RF Cable Assemblies



Documents and Resources

Drawings

731160076_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	RF Cable Assemblies
Series	73116
Description	MCRF Right-Angle Plug to Pigtail on 0.81mm Cable, 230.13mm Length, H18, 50 Ohms
Application	RF
Assembly Configuration	Single Ended Connector
Connector to Connector	MCRF-to-Pigtail
Product Name	MCRF
Type	RF Cable Assembly
UPC	884982813632

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	230.13mm
Gender	Plug/Pigtail
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.800/g
Packaging Type	Individual Bag
Single Ended	Yes
Wire/Cable Type	0.81mm Coaxial

Solder Process Data

Lead-Free Process Capability	Product not active

Obsolete

Mates With / Use With

Downloaded from Arrow.com.

Mates with Part(s)

Description	Part Number
MCRF Cable Assemblies	73412

This document was generated on Sep 11, 2026

Obsolete

Downloaded from Arrow.com.