
Part Number : 732760880
Product Description : N Jack, Straight, 4-Hole Flange Mount, Candlestick Contact, Stainless Steel, Passivated, with Jam Nut, 50 Ohms
Series Number : 73276
Status : Active
Product Category : RF / Coaxial Connectors



Documents and Resources

Drawings

732760880_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73276
Description	N Jack, Straight, 4-Hole Flange Mount, Candlestick Contact, Stainless Steel, Passivated, with Jam Nut, 50 Ohms
Application	RF
Product Name	N
Style	Panel
Type	Medium
UPC	822348027873

Electrical

Frequency	11 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 1000 Vrms@Sea Level

Physical

Cable Attachment	N/A
Gender	Jack
Keying to Mating Part	N/A
Net Weight	29.962/g
Orientation	Straight
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Flange
PCB Mounting	Round Post
PCB Thickness - Recommended	N/A
Reverse Polar	No
Wire/Cable Type	N/A

Downloaded from Arrow.com.

Downloaded from Arrow.com.