


COAXIAL CONNECTOR, MCX, 50 Ohm, Straight bulkhead cable jack (female)
24_MCX-50-2-6/111_N

Properties

- Small size
- Easy to connect and disconnect
- Wide range of board connectors and cable connectors available



Product configuration		
Interface type	Gender	Standard
MCX	jack	IEC 60169-36_CEEC 22220

Interface and material data		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Brass	Gold Plating (Nickel underplated)
Body	Brass	Gold Plating (Nickel underplated)
Insulator	PFA / PTFE	
Fastening nut	Brass	Gold Plating (Nickel underplated)
Washer	Bronze	Gold Plating (Nickel underplated)
Crimp ferrule	Copper	Gold Plating (without Nickel underplating)

Electrical data	
Impedance	50 Ω
Interface frequency	6 GHz

Mechanical data	
Weight	0.0014 kg
Mating cycles	500
Cable entry centre contact	crimped
Cable entry outer contact	crimped

Environmental data	
Operation temperature	-55 °C ... 155°C

COAXIAL CONNECTOR, MCX, 50 Ohm, Straight bulkhead cable jack (female)
24_MCX-50-2-6/111_N

Ordering Information Table		
Item number	Item description	Packaging type
23005300	24_MCX-50-2-6/111_NH	Bulk 100 pcs
Suitable cables		
Cable group	U4 - 2 mm / 50 Ohm	
Suitable cables	K_02252_D	
	G_02232_D	
	ENVIROFLEX_316_D	
Additional Information		
Only as assembly	No	

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2638 / Date of publication: 25.11.2023 / uncontrolled copy