



REV.	DATE	DESCRIPTION
NC	09/28/99	INITIAL RELEASE
A	07/19/05	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS		DATE		Amphenol Connex							
7						DRAWN	G.R.S.		07/19/05								
6						CHECKED											
5							ISSUED					PART DESCRIPTION					
4							SHEET	1 OF 1				BNC EDGE MOUNT RECEPT. JACK – 75ohm					
3	CONTACT PIN	PHOS. BRONZE	GOLD	1								PART NO.					
2	INSULATOR	TEFLON	NATURAL	1								112641					
1	BODY	BRASS	NICKEL	1								DWG. NO.					
DESCRIPTION MATERIAL FINISH QTY					DO NOT SCALE DRAWING	CAD FILE		C:/112/112641.DWG		112641.DWG		REV. A		SIZE A		SCALE NA	