

Product data sheet

Specifications



RACK PDU, BASIC, VERTICAL, 220-240V, 32A, (20) C13, (6) C19

AP6009A

Overview

Lead time Usually in Stock

Main

Product or component type	PDU
PDU type	Basic
Cord length	3.05 m
Number of cables	1
Provided equipment	Installation guide Safety guide

Complementary

Input Voltage	230 V
Height	162.6 cm
Width	5.6 cm
Output Voltage	230 V
Depth	4.3 cm
Net weight	6.18 kg
Mounting location	Side
Mounting preference	No preference
Input Plug Type	IEC 60309 32 A 2P + E
Mounting mode	Not rack-mountable
Rack units	0U
Mounting position	Vertical
Permissible voltage	200...240 V
Input current limits	32 A
Load capacity	7400 VA
Network frequency	50/60 Hz
Outlet type and quantity	20 IEC 60320 C13 6 IEC 60320 C19

Environment

Product certifications	CE EAC IRAM VDE
Ambient air temperature for operation	0...50 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.0000000000...15240.0000000000 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	187.5 cm
Package 1 Width	13.5 cm
Package 1 Length	22.6 cm
Package 1 Weight	8 kg

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Lead Free

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
