Pushing Performance
Since 1945

SEK-18 ACC.STRAIN RELIEF CLAMP FE 16P



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 516 9002
Specification	SEK-18 ACC.STRAIN RELIEF CLAMP FE 16P
HARTING eCatalogue	https://harting.com/09185169002

Identification

Category	Accessories
Series	SEK
Type of accessory	Strain relief clamp

Version

Size	16 poles

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08) + A1 (2023-10)
Requirement set with Hazard Levels	R26

Commercial data

Packaging size	100
Net weight	0.005 g
Country of origin	Romania
European customs tariff number	85389099

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.

Pushing Performance
Since 1945

Commercial data

GTIN	5713140029446
eCl@ss	27440292 Connector component (accessories)
ETIM	EC002943
UNSPSC 24.0	39121400

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany
Phone +49 5772 47-97200 | electronics@HARTING.com | www.HARTING.com

Downloaded from Arrow.com.