Part Number : 1300990114
Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625"), Non-Metallic Mesh
Series Number : 130099
Status : Not Recommended For New Design
Product Category : Cable Grips
Engineering Part Number : 5548NM



Documents and Resources

Drawings

1300990114_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Not Recommended For New Design
Category	Cable Grips
Series	130099
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 1" NPT, Straight Male, Cable Diameter 12.70-15.88mm (.500-.625"), Non-Metallic Mesh
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678855485

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-15.88mm (.500-.625")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	Nylon
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	1" NPT

Mates With / Use With

Downloaded from Arrow.com.

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 1" NPT	1300990145
MAX-LOC Gasket Sealing Ring, 1" NPT, Black	1300990151
MAX-LOC O-Ring, 1" NPT	1301800334

Downloaded from Arrow.com.