



Material Datasheet

13.03.2023

WS3-A

Article Number 597-63200

Material: Type 150, Vinyl (150)

Colour: Yellow (YE)

Operating Temperature : -40 °C to +80 °C

Curing Temperature: from +10 °C

Self adhesive (Yes/No): Yes

Length (L): 50.00 mm

Width of Liner (WL): 100.00 mm

Labels per Sheet: 10 pcs.

Thickness of Foil: 80 µm

Test Method

ASTM D3652-83

Adhesive: Acrylic

Initial tack: 110 g/cm²

Peel strength: 550 N/m

Shear strength: 120 h

ASTM D2979-71

PSTC 7

FINAT FTM 7

We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved



Material Datasheet

13.03.2023

Shelf Life:

Minimum 1 year upon receipt / maximal 2 years after production date.

Storage Temperature:


+21 °C

Storage conditions:

50% relative humidity., The storage in the original packaging is recommended., Please avoid warehousing under impacts such as high humidity, heat and coldness.

Application Method:

The functionality and durability of the labels can be negatively affected if improperly processed or applied. All surfaces to be bonded must be clean, dry as well as free from dust and grease. Avoid touching the adhesive surface of the label as this could impair the application performance.



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved