

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Male Plugs

General Information

Extended Product Type:	L20710400000
Product ID:	1SSA207104R0000
EAN:	3472599014893
Catalog Description:	FIC M VIS 4P/7.62 PAR Male Plugs
Long Description:	Modular mounting (Panel or through panel).

Ordering

Color:	Grey
Minimum Order Quantity:	30 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Weight:	16 g
----------------------------	------

Technical

Rated Cross-Section:	4 mm ²
Spacing:	7.62 mm
Function:	Male Plugs
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 4 mm ² Screw Clamp / Rigid 1x 4 mm ²
Rated Current (I_n):	Main Circuit 25 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 480 A
Rated Voltage (U_r):	380 V
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Wire Stripping Length:	10.0 mm
Recommended Screw Driver:	3.5 mm
Tightening Torque:	acc. IEC 60947-1 0.7 N·m Manufacturer 0.8 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 300 V
Connecting Capacity UL/CSA:	Stranded 12 AWG

Certificates and Declarations (Document Number)

cUL Certificate:	1SND165002A0200
Declaration of Conformity - CE:	1SSD235017C1002

Classifications

Object Classification Code:	X
ETIM 4:	EC002638 - Cable connector
ETIM 5:	EC002638 - Cable connector
ETIM 6:	EC002638 - Cable connector

Container Information

Package Level 1 Units:	30 piece
Package Level 1 Width:	101 mm
Package Level 1 Depth / Length:	265 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.48 kg
Package Level 1 EAN:	3472599014893
Package Level 2 Units:	270 piece
Package Level 3 Units:	12960 piece
Product Packing Type:	Box

