Component housing - HS LC-H-D2/ R4XC2-2,54 - 2202320

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://phoenixcontact.com/download)



Fiber optics can be used for the ME, ME-MAX, ME-IO, ME PLC, and EH housing ranges (housing must be processed), Color: transparent

RoHS

Key Commercial Data

Packing unit	100 STK
Minimum order quantity	100 STK
GTIN	4 055626 050218
GTIN	4055626050218
Weight per Piece (excluding packing)	0.630 g
Custom tariff number	90019000

Technical data

General

Housing type	Fiber optics
Housing material	PC
Color	transparent

Ambient conditions

Ambient temperature (operation)	-40 °C ... 85 °C

Dimensions

Pitch	2.54 mm

Technical data

Flammability rating according to UL 94	HB
Number of positions	8

Standards and Regulations

Flammability rating according to UL 94	HB

Downloaded from Arrow.com.

Component housing - HS LC-H-D2/ R4XC2-2,54 - 2202320


Technical data

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Dimensional drawing



Details on positioning inside the electronics housing can be found in the download area under “Design-In”

Phoenix Contact 2016 © - all rights reserved
http://www.phoenixcontact.com

Downloaded from Arrow.com.