Part Number : 192030094
Product Description : Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier
Series Number : 19203
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : C-S-128-10T



Documents and Resources

Drawings

192030094_sd.pdf

Specifications

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19203
Description	Krimptite Temp-Term Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier
Keyword	Ring Terminal, Ring Terminals
Product Name	Krimptite
Style	Ring, High Temperature
Type	High Temperature Terminal
UPC	800753050051

Agency

UL	E32244

Physical

Barrel Type	Closed
Insulation	None
Material - Plating Mating	Tin
Net Weight	1.292/g
Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Size (AWG)	10, 12
Wire Size mm^2	2.70-6.60

Solder Process Data

Lead-Free Process Capability	N/A

Downloaded from Arrow.com.

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	638851000

This document was generated on Apr 29, 2026

Downloaded from Arrow.com.