
# 100G0111-3.00-9 Product Details





Active

## Spec 99 and Spec 100 Wire and Cable

100G0111-3.00-9

**100G0111-3.00-9**

*TE Internal Number: 3626113001*

Pricing & Availability

Request Sample

Add to My Part List

Buy Product through Distributor

**Product Highlights** View All

- Cable Type = Spec 100G
- Cable Style = Primary
- Wire Size (AWG or Metric) = 3.0 mm²
- Number of Conductors = 1
- General Purpose Application

Documents | Features | Compliance

**Please Note:**
*Use the Product Drawing for all design activity*

### Product Type Features

| | |
|---|---|
| Cable Type | Spec 100G |
| Cable Style | Primary |

### Electrical Characteristics

| | |
|---|---|
| Wire Size (AWG or Metric) | 3.0 mm² |
| Voltage Rating (VAC) | 600 |

### Dimensions

| | |
|---|---|
| Conductor Outer Diameter (mm [in]) | 2.18 [0.086] |

### Body Features

| | |
|---|---|
| Wire Color | White |
| Nominal Outside Diameter (mm [in]) | 2.80 [0.110] |
| Wire Diameter (mm [in]) | 2.80 [0.110] |
| Conductor Type | Tin-Coated Copper |

### Configuration Features

| | |
|---|---|
| Number of Conductors | 1 |

### Industry Standards

| | |
|---|---|
| RoHS/ELV Compliance | RoHS compliant, ELV compliant |
| Lead Free Solder Processes | Not relevant for lead free process |
| RoHS/ELV Compliance History | Always was RoHS compliant |

### Conditions for Usage

| | |
|---|---|
| Temperature Range (°C) | -30 – +105, 150 |

### Operation/Application

| | |
|---|---|
| Application | General Purpose |

### Packaging Features

| | |
|---|---|
| Wire Source | United Kingdom |

### Other

| | |
|---|---|
| Brand | Raychem |
| Node Classification | Hook Up Wire |

**Related Products**

Not quite the product you're looking for?

Find Similar Products

View Part in Product Feature Selector

Check for Tooling



© 2015 TE Connectivity Ltd. family of companies. All Rights Reserved

[+] Provide Website Feedback

Downloaded from Arrow.com.