



Part Number : [191930354](#)

Product Description : VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton

Series Number : 19193

Status : Active

Product Category : Ring and Spade Terminals

Engineering Number : K-390-12

Documents & Resources

Drawings

[Drawing 191930354_sd.pdf](#)

Specifications

[Product Specification PS-19902-011-001.pdf](#)

[Product Specification PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

[Multiple Part Product Compliance Statements](#)

- Eu RoHS
- REACH SVHC
- Low-Halogen

[Multiple Part Industry Compliance Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

[EU RoHS Certificate of Compliance](#)

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 3/0 AWG Wire, Closed-Brazed Barrel, Stud Size 1/2" (M12), Carton
Keyword	Ring Terminal, Ring Terminals
Product Family	VersaKrimp Terminals and Splices
Product Name	VersaKrimp
Type	Ring
UPC	800755052428

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	29.623/g
Packaging Type	Carton
Stud Size	1/2" (M12)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	19.02mm max.
Wire Size (AWG)	3/0
Wire Size mm ²	95.00

Application Tooling

Global

Description	Part Number
-------------	-------------

Die Set (Large) for the HHL Hydraulic Crimper	<u>192900028</u>
Manual tool for Crimping non- insulated 8AWG thru 4/0 Terminals	<u>192940008</u>

This document was generated on Jul 29, 2024