



AMQU000606306R8MA1

Search by :

Part Number

Characteristics

Cross reference



MP

Auto



Closed Magnetic Circuit Type
Molding Processing & for Ultra High Current

Series Pdf




RoHSREACHCoC



Product detail

L(mm) ±	6.8±0.2
W(mm) ±	7.3±0.2
T(mm) ±	2.8±0.2
Inductance(uH)	6.8
Tolerance(±%)	20
Test Frequency	100kHz,0.5V
RDC(Ω)Max	0.049
Isat(A)Typ	6.5
Isat(A)Max	5.5
Irms(A)Typ	5.5
Operating Temperature	−40℃~125℃



Products

- Power Inductor
- EMI-Common Mode Choke
- EMI-Bead
- RF-Signal Inductor
- RF-Passives/Antennas
- LAN Transformer
- Resistor & Current Sensor

Applications

- Automotive
- Industrial
- Server/DataCenter
- Communication
- Mobile and Tablet
- Computer/Laptop
- Consumer

Design Tools

- Simulation Tool
- Product Search Engine
- E-Catalogue

About Us

- Corporate Overview
- Corporate Milestones
- Core Technology
- Certificates & Awards
- Quality and Social Responsibility

Investor

- Financial Information
- Corporate governance
- Stakeholder Contacts

News

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisin](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisin. All rights reserved.