Part Number : 1301550161
Product Description : Watertite Extreme Plug with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/250V/3ø, Cord Grip Body Size F5
Series Number : 130155
Status : Active
Product Category : Wiring Devices
Engineering Part Number : CS83W65



Documents and Resources

Drawings

1301550161_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130155
Description	Watertite Extreme Plug with California Style Locking Blade, 3 Pole/4 Wire, Non-NEMA, 50A/250V/3ø, Cord Grip Body Size F5
IP Rating	IP67
NEMA Configuration	Non-NEMA Locking CA
Product Name	Watertite Extreme
Specialty	N/A
Type	Plug
UPC	78678801466

Agency

CSA	LR6837
UL	E10176

Electrical

Current - Maximum per Contact	50.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F5 1 1/4"
Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A

Downloaded from Arrow.com.

Lighted Connector	No
Locking Blade	Yes
Net Weight	521.177/g
Poles	3-pole/4-wire
Receptacle Type	N/A

Downloaded from Arrow.com.