

**MICRO SWITCH**FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

V3-32

M

DRAWING
NUMBERISSUE
NO.

12

VISIONS

CO20189

OMW

MAY 65

CO21688

MBF

OCT 66

CO31509

RER

JAN 73

CO

36987

SMA

OCT 85

CO74635

KDR

MAY 93

REPLACES

RELEASE NO.

CHECK

27 MAY 65

DLH

CHECK

27 MAY 65

LSD

CHECK



65

21 MAY

OMW

DRAWN

D-50376



NOTE -

1 - TERMINALS ARE PLATED FOR SOLDERING

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 6-14 OZ

RELEASE TRAVEL - - - - - .007 MIN

RELEASE FORCE - - - - - 4 OZ MIN

DIFFERENTIAL TRAVEL - - - - .006-.016

OVERTRAVEL - - - - - .040 MIN

FREE POSITION - - - - - .625 MAX

ELECTRICAL DATACONTACT ARRANGEMENT
S P N O

15.1A 1/2HP 125 OR 250 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 125 VAC "L"

**SCALE FULL**

DO NOT SCALE PRINT

UNLESS OTHERWISE
NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030

TWO PLACE (.00) ± .015

THREE PLACE (.000) ± .005

ANGLES ±

WEIGHT .016 LB