

## Han 24B-gs-M25 (2x24DD)



Image is for illustration purposes only. Please refer to product description.

Part number	19 30 024 1515
Specification	Han 24B-gs-M25 (2x24DD)
HARTING eCatalogue	<a href="https://b2b.harting.com/19300241515">https://b2b.harting.com/19300241515</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han <sup>®</sup> B
Type of hood/housing	Hood
Description of hood/housing	2x Han <sup>®</sup> 24 DD
Type	Low construction

### Version

Size	24 B
Version	Side entry
Cable entry	1x M25
Locking type	Double locking lever
Field of application	Standard hoods/housings for industrial connectors

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP66
	IP67
Type rating acc. to UL 50 / UL 50E	4
	4X
	12



Pushing Performance  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

Approvals	CE DNV GL
-----------	--------------

## Commercial data

Packaging size	1
Net weight	273.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140127210
ETIM	EC000437
eCI@ss	27440202 Shell for industrial connectors