



5 4 3 2 1


SPECIFICATION


Mating Cycles	500
Filter type	C
Capacitance	1000pf±20%
Working Voltage	100v
Current Rating	7.5A
Insulation Resistance	>1GΩ

FREQUENCY (MHz)	ATTENUATION (dB)
5	1dB
10	3dB
50	12dB
100	20dB
500	34dB
1000	30dB



Solder buckets for AWG 20 Max



				Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, Female, Straight 25 Poles, solder buckets, tin plated shell with clinch nuts	Maßstab/ Scale 1.5:1
			Detail.	8-JUL-02	CV			
			Insp.					
			Stand.					
33271	28/11/05	JMDR						
32248	28/10/04	TR						
31058	8-JUL-02	CV						
Mod.	Dat.	Name						

09643117238	M3
09643117237	UNC 4-40
Part number	Nut thread

HARTING EURL
F-95972 Paris



TB 0964311723x	Blatt/ Page 1 / 1
Sub.	