

## FLPR12.0-SBC



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Low Profile Lens, 12.0in. Length, 3mm LED, Super Bi-Color Red/Green

### FEATURES

### VALUE ADDED

### CHECK STOCK

- Wavelength: 645nm / 568nm , Typical Intensity: 100mcd / 60mcd, Color: Red / Green
- Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED
- 4.2mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens