




TOP VIEW



SIDE VIEW



BOTTOM VIEW



## Specifications

Description	Value	Unit
Directivity	Omnidirectional	
Technology	Electret Condenser	
Sensitivity	-42	(dB)
Frequency Range	50 ~ 16,000	(Hz)
Rated Voltage	2	(V)
Output Impedance	2,200	(Ohm)
Connection Method	PC Pins	
Voltage Range	2 ~ 10	(V)
Max Rated Current	0.5	(mA)
Minimum Signal to Noise Ratio	>60	(dB)
Operating Temperature	-20 ~ +60	°C
Storage Temperature	-25 ~ +70	°C

## Notes

- 1) All dimensions are in mm unless otherwise noted  
 2) All parts meet RoHS



DB UNLIMITED

Electret Condenser Microphone

## Revision History

Version	Description			Date	Approved
1	Released from Engineering			10/21/2013	J.S

MO044202-7