

# Product data sheet

Specifications



## 3-Pole Circuit Breaker, 400A, T5 Type for Symmetra PX250/500kW

PD3P400AT5B

### Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

### Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Main Output Voltage	480 V 3 phases 400 V 3 phases
Output connector type	Hard wire 3-wire (3P) 1
Provided equipment	Installation guide

### Physical

Height	43.2 cm
Width	55.9 cm
Depth	54.6 cm
Product weight	6.82 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

### Input

Max line current	400 A
Network frequency	50/60 Hz

### Output

Max current draw	400 A
------------------	-------

### Conformance

Product certifications	CE UL listed
------------------------	-----------------

### Environmental

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	43.2 cm
Package 1 Width	54.6 cm
Package 1 Length	55.9 cm
Package 1 Weight	7.8 kg

## Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------



## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.


[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Use Better

 <b>Materials and Substances</b>	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

### Use Again

 <b>Repack and remanufacture</b>	
Take-back	No