



Part Number : [2127242071](#)

Product Description : Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 7 Circuits, Black

Series Number : 212724

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2127242071_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[2127242071.dxf](#)

Specifications

[2059790000-AS-000.pdf](#)


[2127249200-SPK-200.pdf](#)

[2059790000-PS-000.pdf](#)

[2059790000-PS-002.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains 1,1'-(Ethane-1,2-diyl)bis[pentabromobenzene] per D(2025)7771-DC (04 Feb 2026)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	212724
Description	Micro-One Wire-to-Board Receptacle Housing, 2.00mm Pitch, Single Row, Glow-Wire Capable, 7 Circuits, Black
Application	Signal, Wire-to-Board
Product Name	Micro-One
UPC	193264613878

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	7
Color - Resin	Black
Flammability	94V-0

Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyamide
Net Weight	497.650/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	No
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-One Vertical Single Row Headers	<u>205971</u>
Micro-One Vertical Single Row Headers	<u>217063</u>
Micro-One Right-Angle Single Row Headers	<u>205972</u>
Micro-One Right-Angle Single Row Headers	<u>217064</u>
Micro-One Vertical, Single Row, Through Hole Headers	<u>220029</u>
Micro-One Right-Angle, Single Row, Through Hole Headers	<u>220030</u>

Use with Part(s)

Description	Part Number
Micro-One Female Crimp Terminal, 2.00mm Pitch, Matte Tin Plating, 24-22 AWG, Reel	<u>561349001</u>
Micro-One Female Crimp	<u>561349002</u>

Terminal, 2.00mm Pitch, Matte Tin Plating, 28-26 AWG, Reel	
Micro-One Terminal Position Assurance (TPA) Retainers	<u>212725</u>

This document was generated on Apr 15, 2026