

Technical data sheet

Article number:
116-01812

T18R



Product Group	Cable ties polyamide 6.6 standard
Product Family	T-Series in PA66 coloured
Material	Polyamide 6.6 (PA66)
Colour	Red (RD)
Application Tool	MK3PNSP2, EVOcut, MK7P, MK10-SB, MK20, EVO7, EVO7SP, EVO7i, EVO7iSP
Bundle Ø max.	22.0 mm
Bundle Ø min.	1.5 mm
Flammability	UL 94 V2
Halogen-free	Yes
Height (H)	3.7 mm
Length (L)	100.0 mm
Min.Tensile Strength	80 N
Operating Temperature	-40 °C to +85 °C
Package Content	100 pcs.
Package Content packed in	pack
Releasable Closure (Yes/No)	No
Thickness (T)	1.0 mm
Toothing (Serration)	Inside Serrated
UV-Stabilised	No
Variant	Inside Serrated
Weight/Unit	0.00028 kg
Width (W)	2.45 mm

