

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1120080002

Status:

Active

Overview:

Network Diagnostics Tools

Description:

NetMeter Hand Held Digital DeviceNet and Carrying Case



Documents:	
Drawing (PDF)	Product Literature (PDF)
RoHS Certificate of Compliance (PDF)	

General	
Product Family	Field Attachable / Accessories
Series	112008
Approvals	CE, CUL, CE, UL certified
Comments	NetMeter & Bag; Measures 667 Parameters, NetMeter & Bag; Measures 667 Parameters
Communication Speed	125, 250, 500 Kbaud
I/O Connector	5-pole Micro-Change (M12)
IP Rating	N/A
Material - Contact	N/A
Overview	Network Diagnostics Tools
Product Literature Order No	987650-3281
Product Name	DeviceNet, NetMeter
Type	Hand Held Digital NetMeter®
UPC	78678894652
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	Yes
Diagnostics Port	Yes
Gender	N/A
Keyway	N/A
Material - Connector Body	N/A
Material - Coupling Nut	N/A
Material - Plating Mating	n/a
Net Weight	140.000/g
Orientation	N/A
Poles	N/A
Temperature Range - Operating	0°C to +40°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	N/A
Voltage - Maximum	7-30V DC
Material Info	
Engineering Number	DN-MTR-A
Reference - Drawing Numbers	
Sales Drawing	E-112008-0002-000

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

112008 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION