Part Number: 120087-0241

NC 3P M/MFE 0.5M ST/90 CPLR 24



Series image - Reference only

Status: Active
Series: 120087
Category: Molex Parts
Engineering/Old PN: 443031A10M005

Product Environmental Compliance

EU ELV:Not Reviewed

EU RoHS:Not Reviewed

EU RoHS Phthalates:Not Reviewed

China RoHS:Not Reviewed

REACH SVHC:Not Reviewed

Low-Halogen Status:Not Reviewed

Part Detail

General

Status	**Active**
Category	Molex Parts
Series	120087
UPC	78678849192

Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. Click here to visit the UL Database

CSA	LR6837
UL	E152210

Material Info

Engineering Number	443031A10M005

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

Downloaded from Arrow.com.

[Check our list of old tooling that used to be available for this part]

Products+

- Product Categories
- Product Index
- Industries

Quick Links+

- Company Information
- Contact Molex
- Cross-Reference
- Koch Industries
- Investor Relations
- Literature
- Press Room / Press Releases
- Sitemap
- Terms & Conditions

Resources+

- Supply Chain Transparency
- Business Continuity
- Compliance
- ecocare
- Feedback | Help
- Jobs
- Legal | Trademarks
- Supplier Portal
- Privacy Policy
- Tradeshows

Stay Connected

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018

Downloaded from Arrow.com.