




**Part Number :** [2202002261](#)

**Product Description :** 2.00mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Dual Row, Positive Lock, 26 Circuits, Low-Halogen, Black

**Series Number :** 220200

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[2202002261\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[2202002261.dxf](#)

### Specifications


[2202009200-SPK-200.pdf](#)

[2202000000-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### [Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	Connector Housings
Series	220200
Description	2.00mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Dual Row, Positive Lock, 26 Circuits, Low-Halogen, Black
Application	Signal, Wire-to-Board
Keyword	Micro-Lock Plus 2.0
Product Name	Micro-Lock Plus
UPC	196823498954

### Agency

UL	E29179
----	--------

### Physical

Circuits (maximum)	26
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes

Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	1297.250/mg
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
2.00mm Pitch Micro-Lock Plus Vertical, Dual Row, Surface Mount Headers	<u>220201</u>
2.00mm Pitch Micro-Lock Plus Right-Angle, Dual Row, Surface Mount Headers	<u>220205</u>

### Use with Part(s)

Description	Part Number
2.00mm Pitch Micro-Lock Plus Female Crimp Terminals	<u>505572</u>

---

This document was generated on Apr 22, 2026