Part Number : 936010448
Product Description : Heavy-Duty Crimp Terminal Insert, Male, 12-Pole, 10A, Size 3A «21x21»
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7612.5905.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Crimp Terminal Insert, Male, 12-Pole, 10A, Size 3A «21x21»
Component Type	Inserts - Crimp Contact
Insert Series	S-Q12/0
Product Name	Heavy-Duty Connectors
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191891064

Agency

CSA	256883
UL	E249674

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	400V

Physical

Component Size	3A «21x21»
Durability (mating cycles max)	500
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	11.600/g
Number of Rows	4
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	12

Downloaded from Arrow.com.

Temperature Range - Operating	-40° to +125°C
Tightening Test Torque	0.25 Nm

Mates With / Use With

Mates with Part(s)

Description	Part Number
Heavy-Duty Crimp Terminal Insert, Female, 12-Pole, 10A, Size 3A «21x21»	936010447

Use with Part(s)

Description	Part Number
Use With	Size 3A «21x21» Hoods and Housings

Downloaded from Arrow.com.