



**Part Number :** [1300970272](#)

**Product Description :** Dust-Tight Strain Relief Wide Range Grip, 1 1/2" NPT, Straight Male, Cable Diameter 35.56-44.45mm (1.400-1.750"), Approximate Break Strength 453.59kg (1400 lbs)

**Series Number :** 130097

**Status :** Active

**Product Category :** Cable Grips

**Engineering Part Number :** 36517



---

## Documents and Resources

### Drawings

[1300970272\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Cable Grips
Series	130097
Description	Dust-Tight Strain Relief Wide Range Grip, 1 1/2" NPT, Straight Male, Cable Diameter 35.56-44.45mm (1.400-1.750"), Approximate Break Strength 453.59kg (1400 lbs)
NEMA Rating	Dust Tight
Product Name	Dust-Tight
Type	Strain Relief Grip
UPC	78678836517

#### Agency

CSA	LR32159
UL	E76954

#### Physical

Approximate Break Strength	453.59kg (1400 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	35.56-44.45mm (1.400-1.750")
Color - Grommet	N/A
Eye Type	N/A
Gender	Male
Insulated	Yes
Material - Body	Zinc Plated Steel
Material - Grip	Galvanized Steel

Mesh Length	0.279m (11.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	2" NPT

---

This document was generated on Apr 11, 2026