









Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
Tape on Reel Packaging according to DIN IEC 60286-3
Verpackungseinheit: 400 Stück
Packaging unit: 400 pcs



Verpackung Stange / packaging tube


8	27
6	33
5	37
4	42
3	49
2	58
Polzahl No. of positions	Stück / pieces

Abspulrichtung - Reel off Direction



Layout:

vorgeschlagene Toleranz für PCB Layout ± 0.05
recommended PCB layout tolerance ± 0.05




Material und Oberfläche:
Material and plating:

Gehäuse / housing: LCP, UL94V-0, natural
Kontakt / contact: Kupferlegierung 2.5µm verzinnt, 1.25µm Ni rundum
Copper alloy
2.5µm tin plating over 1.25µm Ni all over


Halteclip / bracket: 2.5µm verzinnt, 1.25µm Ni rundum
Copper alloy
2.5µm tin plating over 1.25µm Ni all over

Maße und Toleranzen in Übereinstimmung mit ASME Y14.5-2009 /
Interpret dimensions according to ASME Y14.5-2009



109906	109912	8	17,3	22,5	14	21,4	44
109905	109911	6	13,3	18,5	10	17,4	44
109904	109910	5	11,3	16,5	8	15,4	32
109903	109909	4	9,3	14,5	6	13,4	32
109902	109908	3	7,3	12,5	4	11,4	24
109901	109907	2	5,3	10,5	2	9,4	24
Ident.-Nr. mit Haube part-no. tape & reel with cap	Ident.-Nr. ohne Haube part-no. tube w/o cap	Polzahl	Mass A	Mass B	Mass C	Mass D	Mass E

Copyright by ERNI Production GmbH & Co. KG
Proprietary notice pursuant to ISO 16061 to be observed.

Information:				Tolerances		 All Dimensions in mm		Scale 5:1				
All rights reserved. Only for Information. To ensure that this is the latest version of this drawing, please contact one of the ERNI companies before using.				Subject to modification without prior notice. Drawing will not be updated.		Designation						
						iBridge male 2mm pitch						
						Single Row Vertical SMT						
b		01.07.2016				www.ERNI.com		109900				I
Index		Date										A3
								Class		IBRIDGE		