





1		2		3		4	5		6		7		8	
插頭部件 (Plug Component)			頭部剝皮尺寸 (Dimensions)			線材規格 (Wire Styls)	尾部剝皮尺寸 (Dimensions)			端子規格 (Termianl Style)				
顏色(Color)	零件描述(Component)	Qty.	內剝(Strip)	外剝(ROJ)	顏色(Color)	SJT 14AWGx3C 105°C 黑色 (Black) Length : 1000±50 (39.4"±2")	外剝(ROJ)	內剝(Strip)	顏色(Color)	規格描述(Instruction)		端子編號(Style No.)		
35P 黑色 (Black)	FM-302L (IEC 60320, C13)	1	6 ⁺¹ ₋₀	18 ± 2	黑/Black(L)		50.8±5	6.35±3	黑/Black(L)	絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated)				
銅本色 (Brass-Natural)	2.0*4.0 方管端子(GEM 98752A-0) (2.0*4.0 Receptacle Terminal)	3	6 ⁺¹ ₋₀	18 ± 2	白/White(N)		50.8±5	6.35±3	白/White(N)	絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated)				
米白色 (Off-White)	G4005-5 品字母插兩件式內模 (Computer 2x4 Serial Housing)	1	6 ⁺¹ ₋₀	18 ± 2	綠/Green(E)		50.8±5	6.35±3	綠/Green(E)	絕緣依尺寸剝除,留膠於線上 (Strip and Retain Outside Insulated)				



FM-302L (IEC 60320, C13, RA)
(Dimensions of Connector Face)



SJT 14AWGx3C截面圖
(Wire Cross-Section)



B-C1 扎線圖示 (Tied Loop Hank Detail)

REV	DATE	REVISE CONTENT
A	08/29-2012	The first edition is issued and drawing.

NOTE:

1. Hi-Pot Test : 1500V/1Sec ; <0.5mA.
2. Insulation Resistance Test : DC 500/min> 100 meg-ohm.
3. Continuity & Polarization Test : No short circuit, break circuit, displacement.
4. Each end terminal shall be capable of withstanding a pull of 25lbs for 1 minutes without loosening.
5. Strain relief shall be capable of withstanding a pull of 35lbs for 1 minutes without loosening.
6. All material according to Non-toxic standard.(Material must be RoHS compliant.)
7. "FMC" logo maybe present on C13.

線材印字 (Wire Printed)	充實, 油墨印字 (Un-Fillers, Printing Ink)			CnC Tech, LLC Industrial Cable and Connector Technology			
包裝方式 (Packing)		DRAWN		CUSTOMER			
Tied Hank	See Hank Detail	Chu8.					
Carton Size	480 x 320 x 200		DATE 08/29-2012	P/N No.	800-1403-2-SJT0-BL-00100		
Pack Number	90pcs/ UL Laster Labels						
Carton Print	See Purchase Order						
TYPE	IEC 60320, C13 RA to ROJ(S&R) Power Supply Cord			MATERIAL	PVC	UNIT	mm
DRAWING NO.	098MM989	REV	A	Customer Approval			