



Part Number : 739290003

Series Number : 73929

Product Category : High-Speed I/O Cable Assemblies


Product Description : Small Form-factor Pluggable (SFP) Cable Assembly, 5.0m Length

Status : New Business Not Supported

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains C,C'-azodi(formamide) per ED/01/2017 (12 January 2017)
EU RoHS	Compliant with Exemption 7(c)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
--------	----------------------------

Category	High-Speed I/O Cable Assemblies
Series	73929
Description	Small Form-factor Pluggable (SFP) Cable Assembly, 5.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	SFP-to-SFP
Product Family	SFP+ and SFP Interconnect Solutions
Product Name	SFP
UPC	800756458762

Electrical

Current - Maximum per Contact	0.5A
Voltage - Maximum	30V

Physical

Cable Length	5.0m
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Gender	Male-Male
Lock to Mating Part	Yes
Material - Resin	Polycarbonate
Net Weight	320.000/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	Twinax
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

This document was generated on Jul 30, 2024