This document was generated on 03/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1302570006
Status: Active
Overview: Brad Micro-Change (M12) Connectors
Description: Micro-Change CC-Link Cordset, 4 Poles, Male (Straight) to Pigtail, 22 AWG, 10.0m (32.81') Length



Series image - Reference only

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E152210

General

Product Family	Industrial Cordsets
Series	130257
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67, IP68
Material - Contact	Copper Alloy
Overview	Brad Micro-Change (M12) Connectors
Product Name	CC-Link, Micro-Change (M12)
Protocol	CC-Link
Type	Single Ended
UPC	78172501836

Physical

Cable Diameter	7.60mm (.299")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Brown
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	723.346/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	0°C to +80°C
Wire Size AWG	22
Wire/Cable Type	Shielded PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number	CC02A-J30-M100

Reference - Drawing Numbers

Sales Drawing	SD-130257-001

EU ELV
Not Relevant

EU RoHS
Compliant with Exemption 6(c)

China RoHS

REACH SVHC
Contained Per - D(2020)9139-DC (19 Jan 2021)
lead

Halogen-Free Status
Not Low-Halogen

For more information, please visit Contact US

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
130257 Series

This document was generated on 03/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.