


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	29MAY'09	SC	JK
	B	REVISED PER ECR-19-009721	01JUL2019	M.G	D.Z







SECTION A-A



NOTE

1 THIS HOUSING ACCEPTS TAB TERMINAL:
-TAB CONTACT: 177917-□(AWG#16-#20)
177916-□(AWG#22-#26)

2 MATING CONN.P/N
-PLUG HSG: 368576-□
-REC CONTACT:177915-□(AWG#16-#20)
177914-□(AWG#22-#26)

3 APPLICABLE DOUBLE LOCK PLATE :177919-1
* IT SHOULD BE USED CERTAINLY WHEN CABLE ASS'Y

4 GENERAL TOLERANCES:±0.3

5 MATERIAL:PA66, UL94V-0,
COMPLY WITH GLOW WIREREQUIREMENT FOR PARTS OF NON-METALLIC MATERIALSUPPORTING A CURRENT-CARRYING CONNECTION DETAILED IN IEC 60335-1, SECTION 30(GWT).

BLUE	2005253-6
YELLOW	2550253-4
NATURAL	2005253-1
COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL 5

FINISH - -

DWN SC KIM -
CHK BW KANG -
APVD JK SONG -
PRODUCT SPEC 108-5410
APPLICATION SPEC 114-5175
WEIGHT -

TE Connectivity

NAME PDL 6P CAP HSG 3.96mm D/R F/H (GWT)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2005253	-

CUSTOMER DRAWING | SCALE 3:1 | SHEET 1 OF 1 | REV B

1470-19 (3/13)

Downloaded from Arrow.com.