Johanson Part Number 2450AT18D0100001E

Johanson Part Number: 2450AT18D0100001E	Johanson Company: JTI
Legacy P/N: 2450AT18D0100E	Size for Capacitors (EIA): None
Description: Antennas, 1206, 2400-2500MHz, 2W, 1.5dBi (typ), Detuning resilient Edge Mount Design, Ni/Sn (RoHS), 7" Reel Embossed Tape	Specification Number: None
Life Cycle Stage: Active	NCNR: No
AEC Q200 Qualified: No	Thickness (Max): 0.055
Schedule B: 8529.10.60.00	Thickness (Min): 0.039
ITAR: No	End Band(Min): 0.00
ECCN: EAR99	End Band (max): 0.016
RoHS Compliance: Yes, RoHS 10/10	Standard Item: Yes
REACH: Yes	Lead Time Typical (Weeks)*: 17
Country of Origin: TW	Length (Min): 0.118
Product Family: Antennas	Length (Max): 0.134
Product Subfamily: Antennas	Width (Min):0.055
Capacitance Value: None	Width (Max): 0.071
Cap Unit of Meas: None	Part Weight (mg): 18.48
Tolerance: None	Packaged Width (lb) Arm: None
Voltage: None	Packaging: 7" Reel Embossed Tape
Dielectric Temp Coefficient: None	Packaging Qty: 3000
Termination: 0	Operating Temp Range: -40°C to +85°C
Marking: Orientation Mark	Storage Temp Range (Packaged): +5°C to +35°C with RH 45% to 75%
Product Release Date: Dec. 30, 2011	Storage Temp Range (None Operating): -40°C to +85°C
Harmonization: 8529.10.60.00	

*This can vary significantly so it is important to obtain a quotation with lead time for production planning purposes.

Web Page Link: https://www.johansontechnology.com/antennas

Printed from: https://www.johansontechnology.com/part/2450AT18D0100001E/

Downloaded from Arrow.com.